



Compact and quick to deploy, the inflatable Mass Decontamination Unit from MFC International allows for rapid response in a decontamination scenario.

Fully inflatable, the Decontamination Unit can be set up in a matter of minutes, and will stay standing without continuous inflation. With no mechanical framework the shelters are relatively lightweight to transport and compact to store.

The mass Decontamination shower is partitioned into three lanes (male, female & assisted casualty), with pre and post decon changing areas.

Partitions are removable and doors can be linked together allowing the shower to be configured as a single, double or triple lane system.

Raised floor panels prevent contact with contaminated shower wash-off, which is collected in a chemically resistant sump. Sleeves for pumped extraction of contaminated water are included as standard.

Showers can be used on hard or soft standing, and guy ropes are provided for securing in position during inclement weather.

FEATURES

- Compact and easily transportable
- Set up within a matter of minutes and will stay standing without continuous inflation
- Flexible internal partitioning with pre and post decontamination changing areas
- Raised floor panels in the shower prevent contact with contaminated shower wash off which is collected in a chemically resistant sump
- Sleeves for portable air heaters and pumped extraction of contaminated water are included as standard
- Shower nozzles are all on demand and can be turned on/off individually
- Windows on internal shower doors with covers, assisted (central) lane door includes zipped flap for transferring medical equipment

- Two inflation/deflation ports allows the use of ARS (automatic refilling system) inflaters for extended deployments
- · Can be used on hard or soft standing
- · Minimal training, servicing and maintenance costs

USED FOR

Decontamination scenarios

SUPPLIED WITH

- Valise (590016)
- Repair kit (600008/01)
- Inflation hose 1m (for use with 8 bar regulator) (HS-04-05-01-27-06)
- Accessories kit bag, containing galvanised ground fixing pegs, rubber mallet and hand pump

MFC International

- **3**: www.mfc-international.com
- **L**: +44 (0) 1443 433 075



| TECHNICAL DATA | Mass Decon Unit | | Mass Decon Unit |
|------------------------|-----------------|--|----------------------|
| Product Code | DSW027 | Max. Water Inlet Pressure (bar) | 3 |
| | DSW027/001 | Recommended Pump Flow-Capacity (Itrs) | 5 ltr/min per nozzle |
| Length (cm) | 726 | Number of Shower Nozzles | 8 |
| Int. Length (cm) | 726 | Number of Shower Hose/Brush Connectors | 8 |
| Width (cm) | 452 | Number of Heater Sleeves | 4 |
| Int. Width (cm) | 406 | Number of Cable sleeves | 8 |
| Height (cm) | 302 | Pack Size (cm) | 160 x 100 x 80 |
| Int. Height (cm) | 278 | Weight (kg) | 140 |
| Int. Floor Area (sq.m) | 30 | | |
| Air Requirements (Itr) | 3800 | | |


CAMLOCK Coupling System


For a system with CAMLOCK couplings throughout order codes in green

Storz Coupling System

For a system with Storz D25 couplings throughout order codes in blue

DETAIL DRAWING






INTERNAL LAYOUT (3 LANE CONFIGURATION)

The diagram on the right shows the different compartments of the Mass Decontamination shower. It also shows how the user enters the decontamination shower and shows the direction of travel. The areas are colour coded:

- Red designates the contaminated area where the user will enter the unit
- Yellow designates the area where the user will wash off any contamination
- **Green** designates the clean, post decontamination area




3: www.mfc-international.com

L: +44 (0) 1443 433 075



SYSTEM SCHEMATIC & COMPONENTS

Using a pillow tank water supply.



Using a tender or stand pipe water supply.

Pressure required: >2 Bar If supply pressure is less than 2 bar 1x inlet water pump (2) will be required

CAMLOCK Coupling System

For a system with CAMLOCK couplings throughout order codes in green

Storz Coupling System

For a system with Storz D25 couplings throughout order codes in blue

SYSTEM COMPONENTS



Clean (Potable) Water Pillow Tank (1000 ltr)

- Other sizes available, see website for details

Quantity Required: x1

Product code: With Camlock Coupling

With Storz Coupling





Inlet Water Pump

Quantity Required: x1 Product code: With Camlock Couplings 240v DSA002 110v DSA010

With Storz Couplings 240v DSA002/001 110v DSA010/001





Water Heater

- Diesel and electric water heater max 50 l/min

Quantity Required: x1

Product code:

With Camlock Couplings

TBC

With Storz Couplings





T-Piece

- Required if the water heater does not have two separate outlets

Quantity Required: x1

Product code:

With Camlock Couplings DSA009 (1xF & 2xM) DSA009/002 (3xM)

With Storz Couplings DSA009/001

3: www.mfc-international.com

L: +44 (0) 1443 433 075



SYSTEM COMPONENTS (CONTINUED)





Dosatron with Trolley -

Required if the water heater does not include an injector for detergent/neutraliser.

Quantity Required: x1 Product code:

With Camlock Couplings DSA005

With Storz Couplings



Mass Decon Shower

Quantity Required: x1
Product code:
With Camlock Coupling

With Storz Coupling

(7)



Submersible (Sump) Pump

Quantity Required: x1 Product code: With Camlock Coupling 240v DSA004 110v DSA003

With Storz Coupling 240v DSA004/001 110v DSA003/001





Dirty (Contaminated) Water Pillow Tank (1000 ltr)

- Other sizes available, see website for details

Quantity Required: x1

Product code: With Camlock Coupling

With Storz Coupling WS0017/002

(9)



Pallets for Decon Floor

Standard Pallet Quantity Required: x6 Product code: 140065 Pallet with Pump Cut-Out Quantity Required: x2 Product code: DSA011





Spray Gun & Hose

Quantity: Up to x8 Product code: DSA008 Short Hose

DSA008/SHORT

(11)



Spray Brush & Hose

Quantity: Up to x8 Product code: 180035 Short Hose 180035/SHORT





Adapter

- To connect fire tender or stand pipe outlet to the decon system in place of a pillow tank and pump.

Quantity Required: x1

Product code:

Various models available depending on outlet coupling - Contact sales for details & product codes

HOSES



Green Clean Water Hose (2m)

Quantity Required: x4
Product code:
With Camlock Couplings
HS-05-02-02-22-22

With Storz Couplings HS-05-02-02-23-23



b Clear Dirty Water Hose (2m)

Quantity Required: x1 Product code: With Camlock Couplings HS-06-06-02-22-22


With Storz Couplings HS-06-06-02-23-23

3: www.mfc-international.com

L: +44 (0) 1443 433 075



ACCESSORY SCHEMATIC







Generator Ford 6kW 4-stroke petrol (190500)





Waterproof LED Interior Lights 23W, 2300 Lumens (4x SLZ2323/5/01DWD - IP67 Lamp) (4x SLZ005 - Hanging kit) 110v 090068





Heater & Ducting Oil fired space heater 20kw (68,000 BTU) heat output SH9150 (1x Heater) (1x High temp air hose)





Waterproof LED Exterior Rechargeable Flood Lights

Solaris Pro 18ah (090065) Solaris Pro 36ah (090066)



Electric Inflater GE1800 Standard 110v - 180057/001 230v - 180058

GE1800 ARS (Auto Refill System)

230v - 180056/001

110v - 180052/001



Patient Conveyor (DSA015) 2.2m Conveyor (2x 210357) 2.4m Conveyor (1x 210358)

Transfer Board (min 1x 210537)

3: www.mfc-international.com

L: +44 (0) 1443 433 075

MFC International